



NOTES:

1. Measured from the centerline of sprocket hole to centerline of the pocket hole and from the centerline of sprocket hole to centerline of the pocket
2. Cumulative tolerance of 10 sprocket holes is  $\pm 0.20$
3. This thickness is applicable as measured at the edge of the tape
4. Material: Conductive Polystyrene
5. Dimensions are in millimeters
6. Allowable camber to be 1mm per 100mm in length, non-cumulative over 250mm
7. Unless otherwise specified, tolerance  $\pm 0.10$
8. Measurement point to be 0.3 from bottom pocket
9. Surface resistivity less than or equal to  $1.0 \times 10^9$  ohms/square
10. Leader / Trailer minimum 75 pockets

**USER FEED  
DIRECTION** →

PACKAGE  
ORIENTATION

