



Notes:

1. Measured from the centerline of sprocket hole to centerline of the pocket hole and from the centerline of sprocket hole to centerline of the pocket.
2. Cumulative tolerance of 10 sprocket holes is ± 0.20 .
3. This thickness is applicable as measured at the edge of the tape
4. Material: Conductive Polystyrene
5. Dimensions are in millimeters.
6. Allowable camber to be 1mm per 100mm in length, non-cumulative over 250mm
7. Unless otherwise specified, tolerance is ± 0.10
8. Measurement point to be 0.3 from bottom pocket
9. Surface resistivity - 1.0×10^5 to 1.0×10^9 ohms/square
10. Measurement point to be 0.3mm from the top of the pedestal
11. Leader / Trailer minimum 75 pockets.