



Notes:

1. 10 sprocket hole pitch cumulative tolerance ± 0.2
2. Camber not to exceed 1mm in 100mm
3. Material: Black Conductive Advantek Polystyrene
4. A_o and B_o measured on a plane 0.3mm above the bottom of the pocket
5. K_o measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
6. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
7. Leader / Trailer minimum 75 pockets

$A_o = 6.95$
 $B_o = 7.10$
 $B_1 = 7.80$
 $K_o = 1.60$
 $K_1 = 1.20$

PACKAGE ORIENTATION

